

Blood glucose meter MEDITOUCH 2

mg/dL Art.-No. 79030 | EAN 40 15588 79030 0

mmol/L Art.-No. 79034 | EAN 40 15588 79034 8

- Precise measurement accuracy according to the new ISO 15197: 2015 thanks to new test strip technology (GDH-FAD)
- USB port for data transfer to VitaDock online
- Underfilling detection
- Acoustic test reminders
- 480 memory slots



Incl. Starter set



Application | Features

- Precise measurement accuracy according to the new ISO 15197: 2015 thanks to new test strip technology (GDH-FAD)
- Underfilling detection
- Acoustic test reminders
- 480 memory slots
- USB port for data transfer to VitaDock Online
- Calculates average values for 7/14/30/90 days
- Pre and post meal markers
- Automatic ketone warning
- Measuring time within 5 seconds
- 0,6 µl amount of blood
- Extra large, easy-to-read display
- Incl. batteries (2 × 3V CR2032)
- Starter set incl. 10 test strips, lancing device, 10 lancets, AST cap, control solution and bag
- Certified medical device*

Technical Data

- Size: approx. 5 × 9,8 × 1,1 cm
- Weight: approx. 0,3 kg
- Batteries: 2 × 3V (CR 2032)

Scope of Delivery

- Blood glucose meter
- Starter set
- Batteries
- Manual

Logistical data

Sales packaging

1 piece | 17,7 x 7,3 x 11,8 cm | 0,24 kg

Packaging unit

4 pieces | 30,5 x 18,7 x 13,4 cm | 1,6 kg

* Certification according to MDD (Medical Device Directive)

