

Product information

00 21 35 LE

Tool Case "Robust23"

Empty



- With a total of 49 inserting options
- Max. payload: 25 kg
- Volume: 23 litres
- For the toughest conditions: Dust-tight, waterproof and temperature-resistant
- Fit-to-fly case, made from impact-resistant polypropylene
- Dustproof and watertight
- Air pressure compensation valve
- Temperature-resistant from - 30°C to +80° C
- Padlock eyelets
- Document compartment; tool boards made from dirt-repelling twin-wall PP sheet with tool pockets and tool straps
- Lockable base tray can be individually divided using aluminium separator system
- Ergonomic dual-component handle

General

Article No.	00 21 35 LE
EAN	4003773077596
Weight	4,800 g
Dimensions	470 x 370 x 190 mm
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details

Dimension exterior (interior) width mm	470 mm (437 mm)
Dimension exterior (interior) height mm	190 mm (172 mm)
Dimension exterior (interior) depth mm	370 mm (307 mm)

technical change and errors excepted





Automatic pressure compensation valve, permeable to air while keeping out water

Two-stage locks, easy to open – also with one hand