

Wireless Motion Detector, indoor



Product ref.: 131776

PRODUCT FEATURES

- Detection range up to 12 m, detection angle approx. 90°, can be rotated 45° smoothly to left and right
- Creep zone protection with second 360° lens
- Filters out brief deviations in brightness
- Variable tripping brightness
- Sabotage protection: battery compartment can only be opened by triggering sabotage contact
- Dimmers and switchers can be assigned directly
- Can be positioned anywhere as it runs on batteries, no wiring work required
- Particularly effective at saving energy, reducing costs and maximising comfort

TECHNICAL DATA

Voltage supply:	3 x Mignon/LR6/AA
Typ. open area RF range:	> 300 m
Radio frequency:	868.3 MHz
Sensing range:	> 12 m
Sensing angle:	approx. 90°
Swivel range:	45°
Battery life:	approx. 1 year
Degree of protection:	IP 20
Dimensions (Ø x H):	55 x 132 mm
Weight:	115 g (without batteries)

LOGISTIC DATA

Product ref.:	131776
EAN code:	4047976317769
Short description:	HM-Sec-MDIR-2
Packaging unit:	48
Size (incl. packaging):	175 x 75 x 75 mm
Weight (incl. packaging):	204.0 g

PACKAGING CONTENT

Operating manual in G and E
 3 x Mignon batteries/LR6/AA
 Mounting material (2 x screws 3,0 x 30,
 2 x plugs 5 mm, 1 x wall mount)

Subject to technical changes.