

Data Sheet

LED Indestructible Keychain Light 1AAA

16701



Designation: 16701

Battery Requirement: 1 x AAA

Bulb required: 5mm cool white LED

Luminous intensity: 12 lm or 28 cd

Range: 10 m (calculated distance at maximum luminous intensity with an illuminance of 0.25lux).

Weight: 19 g (without batteries).

Material: GPPS (General Purpose Polystyrene)
 ABS (Acrylonitrile Butadiene Styrene)
 Rubber
 All contact parts made of bronze or nickel plated steel.

Dimensions (mm):

A	83.2
B	23
C	102
D	

Run Time: 3.5 hours with VARTA HE for High mode

Features (Technical)

- Super bright 5mm cool white LED
- Twist head switch (On/Off)
- 9.1 meters (30 feet) impact resistant
- IPX4 water resistant
- Rubber head & tail cap for maximum durability
- Keychain with carabineer ring
- Anti-roll
- Passed extreme temperature shock test
- 10,000 Switch cycle life