

## Data Sheet

### Power Double USB Built-In Socket

Art. Nr. 67321501

22.10.2020

Input voltage:	8 - 34 Volt DC
Output voltage:	5 Volt DC
Output current max.:	5 A (2 x 2.5 A)
Input current duration:	4.4 A (2 x 2.2 A)
Current consumption:	< 3 mA (open circuit operation)
Overload protection:	yes
Protection against overheating:	yes
Reverse voltage protection:	yes
Connections:	cable end 6 mm tin coated
Panel thickness:	2 mm up to 16 mm
Installation inner diameter :	27.8 mm

#### **Material:**

Housing:	ABS
Temperature stress:	max. 110 °C

#### **Cable:**

Strand:	2 x 0.5 mm <sup>2</sup> red/black
Length:	150 mm

**Power Double USB Built-In Socket**

Art. Nr. 67321501

22.10.2020

