

DATASHEET

LIFY Highflex Cable 0.5 mm² Item no.

Version 11/13

| Jacker, outer dimension | PVC 2.0mm |
|---|--------------------|
| No. of conductors | 100 x 0.08mm |
| Strand per conductor | 0.5 sqmm |
| Color | |
| black/red/green/brown/white/grey/yellow/orange/violet/green-yellow/blue | |
| Packaging | blue spool |
| Length | 10/25/50/100 meter |
| Conductor material | copper |
| Insulation material (with thickness) | PVC 0.6mm |
| Core diameter | 0.8mm |
| Insulation resistance | Min 200M ohm x km |
| Conductor resistance | Max 45 Ω /KM |
| Maximum dielectric strength | 1500V / AC |
| Temperature range | 20 to +70 C |
| Rated voltage | 48V |
| Rated current | 4A |
| Conductor structure | Twisted |



This data sheet is a publication by Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92240 Hirschau (www.conrad.com). All rights including translation reserved. Reproduction by any method, e.g. photocopy, microfilming, or the capture in electronic data processing systems require the prior written approval by the editor. Reprinting, also in part, is prohibited. This data represent the technical status at the time of printing. Changes in technology and equipment reserved.

D) (O O O ...

© Copyright 2013 by Conrad Electronic SE.

Distributed Conrad Electronic SE