

DATASHEET

YV Jumper Wire 0.2 mm²

Version 11/13

Item no.

Jacker, outer dimension.....	PVC 1.1mm
No. of conductors.....	1 x 0.5mm
Strand per conductor.....	0.2 sqmm
Color.....	
black/red/green/brown/white/grey/yellow/orange/violet/green-yellow/blue	
Packaging.....	blue spool
Length.....	25/50/100 meter
Conductor material	Tinned-copper
Insulation material (with thickness).....	PVC 0.3mm
Core diameter.....	0.5mm
Insulation resistance.....	Min 200M ohm x km
Conductor resistance.....	Max 110 Ω /KM
Maximum dielectric strength.....	800V / AC
Temperature range.....	-20 to +70 C
Rated voltage.....	48V
Rated current.....	1.6A
Conductor structure.....	One core