




DIM	MILLIMETERS MIN MAX		DIM	MILLIMETERS MIN MAX		NOTES:
A	29.08	29.85	P	ø3.89	ø4.04	1. DIMENSIONS ARE IN MILLIMETERS. 2. DIMENSIONS AND TOLERANCES PER ASME Y14.5M–1994. 3. 867C–01 THRU –04 OBSOLATE, NEW STANDARD 867C–05. 3. STYLE 1: