



Metal angle bracket, including M20 cable gland

Part no. SL7/4-FW-T
Catalog No. 171455
Alternate Catalog No. SL7/4-FW-T
EL-Nummer (Norway) 4137710

Delivery program

Product range			Accessories
Basic function accessories			Including mounting bracket M20 cable gland
Material			Stainless steel (angle) Aluminium (Gewindeadapter)
Mounting type			for vertical mounting
			Gasket included as standard
For use with			SL4-PIB-T... SL7-CB-T...
Connection to SmartWire-DT			no

Design verification as per IEC/EN 61439

Technical data for design verification			
Operating ambient temperature min.		°C	-30
Operating ambient temperature max.		°C	60

Technical data ETIM 7.0

Low-voltage industrial components (EG000017) / Wall bracket for signal tower (EC001153)			
Electric engineering, automation, process control engineering / Low-voltage switch technology / Command and alarm device / Signal column element, attaching bracket (ecI@ss10.0.1-27-37-12-33 [AKF051014])			
Mounting method			Wall mounting
Colour			Other

Approvals

Product Standards			IEC/EN 60947-5-1; UL 508; CSA-C22.2 No. 14-10; CSA-C22.2 No. 94-91; CE marking
UL File No.			E29184
UL Category Control No.			NKCR
CSA File No.			UL report applies to both US and Canada
CSA Class No.			NKCR7
North America Certification			UL listed, certified by UL for use in Canada
Degree of Protection			UL Type 4, 4X, 13

Dimensions

