



MB310 PCB Terminal Block, Single Mold /Modular



DIMENSIONS/POSITIONS

DIMENSIONS/POSITIONS		MB310-500	MB310-500M
間距	Pitch	5.00mm	5.00mm
位數	Poles	2 ~ 24Poles	2 ~ 3Poles
尺寸a	Dimension a	5.00mm	5.00mm
長度 A	Length	A= 5.00xP(P≥2)	A= 5.00xP(P≥2)
塑膠本體	Housing Material	PA 66	PA 66
壓線圈	Cage Clamp	Steel	Steel
端子	Contact	Brass, Tin Plated	Brass, Tin Plated
螺紋	Screw Thread	M2.6, Steel, Zinc Plated	M2.6, Steel, Zinc Plated
電線線徑	Wire Size	12 ~ 26AWG	12 ~ 26AWG
PCB孔徑	PCB Hole Diameter	1.5mm	1.5mm
最大緊固扭矩	Tightening Torque, Max.	7.0 Lb-in	7.0 Lb-in
環境作業溫度	Operating Temperature	-40°C to +105°C	-40°C to +105°C

TECHNICAL DATA

連接符合標準 Connection in acc. with standard EN-VDE			
額定電流 _{IN}	Nominal Current _{IN}	16A	16A
額定橫截面	Nominal Cross Section	4.0mm ²	4.0mm ²
最大負載電流	Maximum load current	16A	16A
絕緣材料	Insulating Material	PA	PA
阻燃等級, 符合UL94 Inflammability class acc. to UL94		V0	V0
額定電壓, UL/CUL Nominal voltage, UL/CUL		300V	300V
額定電流, UL/CUL Nominal current, UL/CUL		16A	16A

