

Phaesun Ceiling Fan PN-CF-RC 12 V

Phaesun Ceiling Fans are high efficiency DC ceiling fans. Thanks to a thermal bridge concept Phaesun Ceiling Fans for direct current outclass AC fans by a factor of 4 to 6 in consumption and competing DC fans by more than a factor of 2 when comparing the same air performance in the medium speed range.

Features:

- 3 metal blades, white finish
- Input 12 V with remote control
- 6 speed, rpm 240



Technical Data	PN-CF-RC 12 V					
Nominal voltage [VDC]	12					
Speed / Stage	6	5	4	3	2	1 (max)
Current [A]	0.150	0.207	0.308	0.478	0.740	1.180
Power [W]	1.80	2.48	3.67	5.74	8.88	14.16
Speed [rpm]	50	85	119	152	191	239
Air delivery [m ³ /h]	2,544	4,325	6,055	7,735	9,722	12,165
Blade diameter [mm]	1,320					
Weight [kg]	7.0					
Article No.	360084					

Phaesun Ceiling Fan PN-CF-RC 24 V

Phaesun Ceiling Fans are high efficiency DC ceiling fans. Thanks to a thermal bridge concept Phaesun Ceiling Fans for direct current outclass AC fans by a factor of 4 to 6 in consumption and competing DC fans by more than a factor of 2 when comparing the same air performance in the medium speed range.

Features:

- 3 metal blades, white finish
- Input 24 V with remote control
- 6 speed, rpm 240



Technical Data	PN-CF-RC 24 V					
Nominal voltage [VDC]	24					
Speed / Stage	6	5	4	3	2	1 (max)
Current [A]	72	100	151	230	365	524
Power [W]	1.73	2.40	3.62	5.52	8.76	12.58
Speed [rpm]	50	87	120	153	193	227
Air delivery [m ³ /h]	2,548	4,428	6,108	7,790	9,825	11,555
Blade diameter [mm]	1,320					
Weight [kg]	7.0					
Article No.	360085					