

# PMK ARCA 60



Sample image

**Order symbol:** PMK ARCA 60

**Product nbr:** 8120844

**Description:** PoleMounting kit. for pole  
ø100-300mm

**Remarks:** For sizes 400x600x210.  
800x600x300

**Including:**

**EAN:** 6418074083241

**EI. number:**

- Finland: 3424029
- Denmark: 8212095096
- Sweden: 2500212

| Dimensions: | Height | Width | Depth |
|-------------|--------|-------|-------|
| mm:         | 585    | 385   | 35    |
| inch:       | 23.03  | 15.16 | 1.38  |

## Materials:

Material:

Base colour:

Cover colour:

Gasket material:

## Rating:

Ingress protection (EN 60529):

Impact Resistance (EN 62262):

Electrical insulation: Not insulated

Halogen free (DIN/VDE 0472, Part 815): 0

UV resistance: -

Flammability Rating:

Glow Wire Test (IEC 695-2-1) °C: C

NEMA Class

## Temperatures:

Temperature °C (short term):

Temperature °C (continuous):

Temperature °F (short term):

Temperature °F (continuous):

## Certificates: