

Chip Resistance Set

Content Set 12100 parts
100 pieces each resistance-value

Tolerance ± 1 %

Power Rating
0402 · 1/16 W
0603 · 1/10 W
0805 · 1/8 W
1206 · 1/4 W

Temperature -55 - +155 °C



The Resistors can be ordered individually, or like a complete Reel.

Content each Reel:

Kit 0402 · 10.000 pieces

Kit 0603, 0805, 1206 · 5.000 pieces

Pos.	Resistance Value	Order-No. 1209137 Kit 0402		Order-No. 1209138 Kit 0603		Order-No. 1209139 Kit 0805		Order-No. 1209140 Kit 1206	
		Piece	Reel	Piece	Reel	Piece	Reel	Piece	Reel
1	0 Ω	1208228	1209874	1208477	1210252	1208621	1210494	1208874	1210693
2	10 Ω	1208229	1209875	1208478	1210253	1208622	1210495	1208875	1210694
3	11 Ω	1208230	1209876	1208479	1210254	1208623	1210496	1208876	1210695
4	12 Ω	1208231	1209877	1208480	1210255	1208624	1210497	1208877	1210696
5	15 Ω	1208232	1209878	1208481	1210256	1208625	1210498	1208878	1210697
6	16 Ω	1208233	1209879	1208482	1210257	1208626	1210499	1208879	1210698
7	18 Ω	1208234	1209881	1208483	1210258	1208627	1210500	1208880	1210699
8	20 Ω	1208235	1209883	1208484	1210259	1208628	1210501	1208881	1210700
9	22 Ω	1208236	1209885	1208485	1210260	1208629	1210502	1208882	1210701
10	24 Ω	1208237	1209886	1208486	1210261	1208630	1210503	1208883	1210702
11	27 Ω	1208238	1209887	1208487	1210262	1208631	1210504	1208884	1210703
12	30 Ω	1208239	1209888	1208488	1210263	1208632	1210505	1208885	1210704
13	33 Ω	1208240	1209889	1208489	1210264	1208633	1210506	1208886	1210705
14	36 Ω	1208241	1209890	1208490	1210265	1208634	1210507	1208887	1210706
15	39 Ω	1208242	1209891	1208491	1210266	1208635	1210508	1208888	1210707
16	43 Ω	1208243	1209892	1208492	1210267	1208636	1210509	1208889	1210708
17	47 Ω	1208244	1209893	1208493	1210268	1208637	1210510	1208890	1210709
18	51 Ω	1208245	1209894	1208494	1210269	1208638	1210511	1208891	1210710
19	56 Ω	1208246	1209895	1208495	1210270	1208639	1210512	1208892	1210712
20	62 Ω	1208247	1209896	1208496	1210271	1208640	1210513	1208893	1210714
21	68 Ω	1208248	1209897	1208497	1210272	1208641	1210514	1208894	1210716
22	75 Ω	1208249	1209898	1208498	1210273	1208642	1210515	1208895	1210718
23	82 Ω	1208250	1209899	1208499	1210274	1208643	1210516	1208896	1210720
24	91 Ω	1208251	1209900	1208500	1210275	1208644	1210517	1208897	1210722
25	100 Ω	1208252	1209901	1208501	1210276	1208645	1210518	1208898	1210724
26	110 Ω	1208253	1209902	1208502	1210277	1208646	1210519	1208899	1210726
27	120 Ω	1208254	1209903	1208503	1210278	1208647	1210520	1208900	1210728

Pos.	Resistance Value	Order-No. 1209137 Kit 0402		Order-No. 1209138 Kit 0603		Order-No. 1209139 Kit 0805		Order-No. 1209140 Kit 1206	
		Piece	Reel	Piece	Reel	Piece	Reel	Piece	Reel
28	130 Ω	1208255	1209904	1208504	1210279	1208648	1210521	1208901	1210730
29	150 Ω	1208256	1209905	1208505	1210280	1208649	1210522	1208902	1210732
30	160 Ω	1208257	1209906	1208506	1210281	1208650	1210523	1208903	1210735
31	180 Ω	1208258	1209907	1208507	1210282	1208651	1210524	1208904	1210737
32	200 Ω	1208259	1209908	1208508	1210283	1208652	1210525	1208905	1210739
33	220 Ω	1208260	1209909	1208509	1210284	1208653	1210526	1208906	1210740
34	240 Ω	1208261	1209910	1208510	1210285	1208654	1210527	1208907	1210741
35	270 Ω	1208262	1209911	1208511	1210286	1208655	1210528	1208908	1210742
36	300 Ω	1208263	1209912	1208512	1210287	1208656	1210529	1208909	1210743
37	330 Ω	1208264	1209913	1208513	1210288	1208657	1210530	1208910	1210744
38	360 Ω	1208265	1209914	1208514	1210289	1208658	1210531	1208911	1210745
39	390 Ω	1208266	1209915	1208515	1210290	1208660	1210532	1208912	1210746
40	430 Ω	1208267	1209916	1208516	1210291	1208661	1210533	1208913	1210747
41	470 Ω	1208268	1209917	1208517	1210292	1208662	1210534	1208914	1210748
42	510 Ω	1208269	1209918	1208518	1210293	1208663	1210535	1208915	1210749
43	560 Ω	1208270	1209919	1208519	1210294	1208664	1210536	1208916	1210750
44	620 Ω	1208271	1209920	1208520	1210295	1208665	1210537	1208917	1210751
45	680 Ω	1208272	1209921	1208521	1210296	1208666	1210538	1208918	1210752
46	750 Ω	1208273	1209922	1208522	1210297	1208667	1210539	1208920	1210753
47	820 Ω	1208274	1209923	1208523	1210298	1208668	1210540	1208921	1210754
48	910 Ω	1208275	1209924	1208524	1210299	1208669	1210541	1208922	1210755
49	1 kΩ	1208276	1209925	1208525	1210300	1208670	1210542	1208923	1210756
50	1.1 kΩ	1208277	1209926	1208526	1210301	1208672	1210543	1208924	1210757
51	1.2 kΩ	1208278	1209927	1208527	1210302	1208673	1210544	1208925	1210758
52	1.3 kΩ	1208279	1209928	1208528	1210303	1208674	1210545	1208926	1210759
53	1.5 kΩ	1208280	1209929	1208529	1210304	1208675	1210546	1208927	1210760
54	1.6 kΩ	1208281	1209930	1208530	1210305	1208676	1210547	1208928	1210761
55	1.8 kΩ	1208282	1209931	1208531	1210306	1208677	1210548	1208929	1210762
56	2 kΩ	1208283	1209932	1208532	1210307	1208678	1210615	1208930	1210763
57	2.2 kΩ	1208284	1209933	1208533	1210308	1208679	1210549	1208931	1210764
58	2.4 kΩ	1208285	1209934	1208534	1210309	1208680	1210550	1208932	1210765
59	2.7 kΩ	1208286	1209935	1208535	1210310	1208681	1210551	1208933	1210766
60	3 kΩ	1208287	1209936	1208536	1210311	1208682	1210552	1208934	1210767
61	3.3 kΩ	1208288	1209937	1208537	1210312	1208683	1210553	1208935	1210768
62	3.6 kΩ	1208289	1209938	1208538	1210313	1208684	1210554	1208936	1210769
63	3.9 kΩ	1208290	1209939	1208539	1210314	1208685	1210555	1208937	1210770
64	4.3 kΩ	1208291	1209940	1208540	1210315	1208686	1210556	1208938	1210771
65	4.7 kΩ	1208292	1209941	1208541	1210316	1208687	1210557	1208939	1210772
66	5.1 kΩ	1208293	1209942	1208542	1210317	1208688	1210558	1208940	1210773
67	5.6 kΩ	1208294	1209943	1208543	1210318	1208689	1210559	1208941	1210774
68	6.2 kΩ	1208295	1209944	1208544	1210319	1208690	1210560	1208942	1210775
69	6.8 kΩ	1208296	1209945	1208545	1210320	1208691	1210561	1208943	1210776
70	7.5 kΩ	1208297	1209946	1208546	1210321	1208692	1210562	1208944	1210777
71	8.2 kΩ	1208298	1209947	1208547	1210322	1208693	1210563	1208945	1210778
72	9.1 kΩ	1208299	1209948	1208548	1210323	1208694	1210564	1208946	1210779
73	10 kΩ	1208300	1209949	1208549	1210324	1208695	1210565	1208947	1210780
74	11 kΩ	1208301	1209950	1208550	1210325	1208696	1210566	1208948	1210781

Pos.	Resistance Value	Order-No. 1209137 Kit 0402		Order-No. 1209138 Kit 0603		Order-No. 1209139 Kit 0805		Order-No. 1209140 Kit 1206	
		Piece	Reel	Piece	Reel	Piece	Reel	Piece	Reel
75	12 kΩ	1208302	1209951	1208551	1210326	1208697	1210567	1208949	1210782
76	13 kΩ	1208303	1209952	1208552	1210327	1208698	1210568	1208950	1210783
77	15 kΩ	1208304	1209953	1208553	1210328	1208699	1210569	1208951	1210784
78	16 kΩ	1208305	1209954	1208554	1210329	1208700	1210570	1208952	1210785
79	18 kΩ	1208306	1209955	1208555	1210330	1208701	1210571	1208953	1210786
80	20 kΩ	1208307	1209956	1208556	1210331	1208702	1210572	1208954	1210787
81	22 kΩ	1208308	1209957	1208557	1210332	1208703	1210573	1208955	1210788
82	24 kΩ	1208309	1209958	1208558	1210333	1208704	1210574	1208956	1210789
83	27 kΩ	1208310	1209959	1208559	1210334	1208705	1210575	1208957	1210790
84	30 kΩ	1208311	1209960	1208560	1210335	1208706	1210576	1208958	1210791
85	33 kΩ	1208312	1209961	1208561	1210336	1208707	1210577	1208959	1210792
86	36 kΩ	1208313	1209962	1208562	1210337	1208708	1210578	1208960	1210794
87	39 kΩ	1208314	1209963	1208563	1210338	1208709	1210579	1208961	1210795
88	43 kΩ	1208315	1209964	1208564	1210339	1208710	1210580	1208967	1210796
89	47 kΩ	1208316	1209965	1208565	1210340	1208711	1210581	1208968	1210797
90	51 kΩ	1208317	1209966	1208566	1210341	1208712	1210582	1208969	1210798
91	56 kΩ	1208318	1209967	1208567	1210342	1208713	1210583	1208970	1210799
92	62 kΩ	1208319	1209968	1208568	1210343	1208714	1210584	1208971	1210800
93	68 kΩ	1208320	1209969	1208569	1210344	1208715	1210585	1208972	1210801
94	75 kΩ	1208321	1209970	1208570	1210345	1208716	1210586	1208973	1210802
95	82 kΩ	1208322	1209971	1208571	1210346	1208717	1210587	1208974	1210803
96	91 kΩ	1208323	1209972	1208572	1210347	1208718	1210588	1208975	1210804
97	100 kΩ	1208324	1209973	1208573	1210348	1208719	1210589	1208976	1210805
98	110 kΩ	1208325	1209974	1208574	1210349	1208720	1210590	1208977	1210806
99	120 kΩ	1208326	1209975	1208575	1210350	1208721	1210591	1208978	1210807
100	130 kΩ	1208327	1209976	1208576	1210351	1208722	1210592	1208979	1210808
101	150 kΩ	1208328	1209977	1208577	1210352	1208723	1210593	1208980	1210809
102	160 kΩ	1208329	1209978	1208578	1210353	1208724	1210594	1208981	1210810
103	180 kΩ	1208330	1209979	1208579	1210354	1208725	1210595	1208982	1210811
104	200 kΩ	1208331	1209980	1208580	1210355	1208726	1210596	1208983	1210812
105	220 kΩ	1208332	1209981	1208581	1210356	1208727	1210597	1208984	1210813
106	240 kΩ	1208333	1209982	1208582	1210357	1208728	1210598	1208985	1210814
107	270 kΩ	1208334	1209983	1208583	1210358	1208729	1210599	1208986	1210815
108	300 kΩ	1208335	1209984	1208584	1210359	1208730	1210600	1208987	1210816
109	330 kΩ	1208336	1209985	1208585	1210360	1208731	1210601	1208988	1210817
110	360 kΩ	1208337	1209986	1208586	1210361	1208732	1210602	1208989	1210818
111	390 kΩ	1208338	1209987	1208587	1210362	1208733	1210603	1208990	1210819
112	430 kΩ	1208339	1209988	1208588	1210363	1208734	1210604	1208991	1210820
113	470 kΩ	1208340	1209989	1208589	1210364	1208735	1210605	1208992	1210821
114	510 kΩ	1208341	1209990	1208590	1210365	1208736	1210606	1208993	1210822
115	560 kΩ	1208342	1209991	1208591	1210366	1208737	1210607	1208994	1210823
116	620 kΩ	1208343	1209992	1208592	1210367	1208738	1210608	1208995	1210824
117	680 kΩ	1208344	1209993	1208593	1210368	1208739	1210609	1208996	1210825
118	750 kΩ	1208345	1209994	1208594	1210369	1208740	1210610	1208997	1210826
119	820 kΩ	1208346	1209995	1208595	1210370	1208741	1210611	1208998	1210827
120	910 kΩ	1208347	1209997	1208596	1210371	1208742	1210612	1208999	1210828
121	1 MΩ	1208348	1209998	1208597	1210372	1208743	1210613	1209000	1210829