

TIP-Meter

3/16 + 3/32 MID

- Digital three-phase power meter for sub-metering
- Integrated meter: SINUS 85 S0 MID
- Accuracy class B
- MID-approved
→ approved for allocation
- Protection class IP44
- Available with CEE-plug connectors (6h) or without plug
- Transparent protective hood for operating the meter



MADE IN GERMANY

Further information to find on
www.stromzaehler.de

Item No.:	41600	41602	43201	43202
Nominal voltage	3 x 230 (400) V			
Nominal-(max.-)current	5 (16) A		5 (32) A	
Nominal frequency	50 Hz			
Accuracy class	Class 1 (B)			
Temperature range	-25°C ... +55°C			
Backstop	•	•	•	•
CEE-plug connectors	•		•	

Measurements

Total length:	140 cm
Height housing:	10 cm
Width housing:	10 cm
Length housing:	18 cm