

## TIP Three-Phase-Outdoor power meter 3/16 and 3/32

Approved for allocation

The TIP-Meter 3/16 and 3/32 are three-phase power meters with included MID-certified meter SINUS 85 made by TIP. The housing is impact- and weatherproof according to IP65. The cable is 0,5m long on each side of the meter, ending in CEE plug connectors for 16 or 32 Amperes. On customer request custom lengths of the cables are possible. The maximum power of the meter is limited by the built-in plug connectors.



This meter is the ideal solution for your purpose.  
For exhibition-stands, campgrounds, garden plots,  
your hobbies, marina etc.

### Technical specification

MID Approval:	Yes
Nominal voltage:	3x230/400V, 50Hz
Nominal current:	3x16A oder 3x32A
Accuracy class:	B (+/-1%)
Cable length:	0,5m - custom length on request
Safety class housing:	IP 65
Safety class CEE plugs	IP 44
Display:	6 + 2 digits (123456,78 kWh)
Temperature range:	-25 ... +75 °C

TIP Thüringer Industrie Produkte GmbH  
Bahnhofstraße 26, 99842 Ruhla, Germany  
Phone: +49 (0)36929/64029-0  
Fax: +49 (0)36929/64029-99  
E-Mail: [info@stromzaehler.de](mailto:info@stromzaehler.de)  
Internet: <http://www.stromzaehler.de>

Final clearance:  
Ruhla,  
Signature: