


TF-3003BMRX6FT Technical Data

8.9cm TFT resolution	320X 240 Pixels
Lens sensor resolution	640 x 480 Pixels
Sensitivity	1.8V (Lux,sec)
Color Mosaic	RGB Bayer pattern
White comparison	Automatic
Exposure to light	Automatic
Camera illumination	4 LEDs, white
Powered by	4 x 1.5V  AA batteries
Power Consumption	Max 600 mA
TV Cable length	Approx. 1.5 M
Total length of device	205.0 ± 2.0 cm
Metal tube length	175.0 ± 2.0 cm
Minimum bending radius	4.5 cm
Diameter of camera head	8.0 mm
Lens coverage	54°
Operating temperature	0 to+45°C
Operating Humidity	15 - 85% RH
Storage temperature	.-10 to +50°C
Storage Humidity	15 - 85% RH
Short distance focus	6cm - ∞
Weight without accessories	Approx. 550 gm
Micro SDHC slot	Support Micro SDHC up to 32 GB
Zoom	Maximum to 4.0 times

Dated 2013.7.29