

PRODUCT DATA SHEET

3943pv

Insulated sleeves – 3943 PVC 6.3/2.5



Product Overview

SKU	3943pv
Part description	Insulated sleeves
Part designation	3943 PVC 6.3/2.5


Material

Component	Polyvinylchloride (PVC)
Surface	Transparent

Technical Details

Net weight kg/1000	0.560
Conductor cross-section	0.5 – 2.5mm ² / AWG 20 – 14
Plug-in size	6.30mm
Hardness	Shore A 70 +/-5
Dielectric strenght	>20 kV/mm
Temperature resistance	-25°C to +70°C
Flammability	UL94/HB

Dimensions



© 2022 | Vogt AG Verbindungstechnik

The general conditions of sale of Vogt AG apply to this product. See www.vogt.ch/downloads.

This data sheet is regularly revised but is not subject to any change service.

This article is a freely available article according to the above specification. The availability of certificates according to EN 10204, others acceptance test certificates or material compliance and customer-specific part submission warrant, are to be requested by the customer and, if available, can be obtained for a fee.

You can find more information on the free available product conformities at www.vogt.ch/downloads.

Form checked and approved special field: 17.02.2022 haatob
Form created: 17.02.2022 haatob

PDS_3943pv_EN_V1.docx
Content created: 04.06.24 karlea / Version: 01

Page 1 / 1
PM-FO-03 / Version: 00

Vogt AG Verbindungstechnik
+41 62 285 75 75

Duschletenstrasse 2 – 4
info@vogt.ch

4654 Lostorf / Switzerland
www.vogt.ch