Coupler connector - CA-17S1N8A90DN - 1620149

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (http://download.phoenixcontact.com)



The figure shows the 12-pos. product version

Coupling connector, straight, shielded: Yes, SPEEDCON locking, M23, Number of positions: 17, Type of contact: Socket, Crimp connection, Cable diameter: 3 mm ... 14.5 mm

Key commercial data

package_quantity	1
GTIN	4046356818957

classifications

eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	272607xx
eCl@ss 5.0	27260701
eCl@ss 5.1	27260701
eCl@ss 6.0	27260702
eCl@ss 7.0	27440102
eCl@ss 8.0	27440102

ETIM

ETIM 3.0	EC001121
ETIM 4.0	EC002635
ETIM 5.0	EC002635

UNSPSC

UNSPSC 6.01	43172015
UNSPSC 7.0901	43201404
UNSPSC 11	43172015
UNSPSC 12.01	43201404
UNSPSC 13.2	43201404

accessories

Protective cover

Coupler connector - CA-17S1N8A90DN - 1620149

accessories

SF-Z0019 - 1607449



RC-Z2059 - 1604225




RC-Z2469 - 1611797




Drawings

Dimensioned drawing



Coupler connector - CA-17S1N8A90DN - 1620149

Schematic diagram



© Phoenix Contact 2014 - all rights reserved
http://www.phoenixcontact.com