

Testboy Profi III LED+°

Two-pole voltage tester with FI-Test

The new Testboy Profi III LED+° is the consequential further development of our popular Testboy Profi LED Plus . It convinces due to its user-friendly handling, the robust, safe construction and conforms to all requirements placed on modern voltage testers by a specialist .

How you benefit

- | Practical one-hand operation
- | Robust, safe construction
- | Testing without finger contact
- | Indication of voltages also possible without battery



SPECIFICATIONS

	Testboy Profi III LED+°
Display	Optical, LEDs
Ranging	automatic
Voltage range	6 – 1000 V AC 6 – 1400 V DC
Overtoltage category	CAT IV 400V /CAT III 750V
Continuity testing	0 – 50 kΩ optically/acoustically
Phase indication	> 100 V AC
Single-pole phase testing	Yes
Two-pole phase sequence testing	Yes
FI/RCD check test	30 mA at 230 V AC using two buttons
Diode test	Yes
Polarity	Yes (+,- LED)
PELV indication	optical acoustic and vibrating
Measurement position lighting	white LED
Auto-Power-Off	Yes
4-mm test tip adapter	Removable
Protection class	IP 65
Standard	EN 61243-3:2010
Dimensions	300 × 75 × 20 mm
Weight	270 g
Power supply	2 × 1.5 V AAA (indication of voltages also possible without battery)
Colour	Red/black
Scope of delivery	Incl. batteries
Accessories (optional)	Carrying case

