

AV Konverter **SpeaKa Professional** VGA to HDMI



Product Feature

- Video and audio in full digital HDMI format, no transmission loss!
- Supports standard VESA VGA timing output .HDMI output support up to 1920x1080@60Hz.
- Provides advanced signal and processing with great precision colors.
- No need external power adapter (supporting VGA port and internal power supply)
- No need drive software, plug and play
- Resolutions Automatically identify the HDTV or monitor EDID by DDC channel.
- Adapt to HDTV or DVI monitor automatically
- No power adaptor, no messy cords—just one HDMI cable.
- Hassle Free! Plug and play.

Technical data

- Supported input/output Mode:

640x480@60/75Hz ,
800x600@60/75Hz,
1024x768@75Hz,
1152x864@60/75Hz,
1280x600@60Hz,
1280x720@60Hz,
1280x768@60/75Hz,
1280x800@60Hz,
1280x960@60Hz,
1280x1024@60/75Hz,
1360x768@60Hz,
1366x768@60Hz,
1400x1050@60Hz,
1440x900@60Hz,
1600x900@60Hz,
1600x1200@60Hz,
1680x1050@60Hz,
1920x1080@60Hz,

- Video Input VGA(RGBHV)

- HDMI Output compatible with HDMI 1.3

- Connector VGA/HDMI

- Input Signal RGB: 0.7 Vp-p 75 ohm

H + V 3 to 5 Vp-p

- Audio Input Analog audio L,R

- External Power Supply USB Power(500mA)

- Power Consumption : 0.5 watts (max)

Standard data

- Dimensions 72 x 41 x 18 mm (L x w x h)

- Weight : 12g

- USB power Cable, length 1M

- VGA Cable length, 20cm

- Audio Cable length 1M

- Operating Temperature 0 to +70 degree C

- Operating Humidity 10% to 85 % RH (no condensation)

- Storage Temperature : -10 to +80 degree C

- Storage Humidity : 5% to 90 % RH (no condensation)