

FOR A GOOD REASON
GRUNDIG



Volume Hood Dryer HS 6780

Product data

- 450 W output
- **Ionic technology** ensures easier styling, more shine and less static charging
- **Gentle drying system** with integrated **cool shot** gives prolonged volume, resilient and strong curls
- Efficient professional motor reduces drying time
- **2 heat and speed settings**
- Individually adjustable comfortable support belt
- 3 m extra long power cord
- 1 LED for ionic function
- Comfortable cosmetic case
- Mains operation 220-240 V~, 50-60 Hz
- Colour: silver / lightgreen metallic



Comfortable cosmetic case



Model number	HS 6780
Order number	GML 8300
Packaging unit	6
Bar code	4013833611394
RRP*	

* recommended retail price of Grundig Intermedia GmbH