



KP 1071



Induction Cooker

Colour / Material: black

Output: approx. 2000 W

EAN-no.: 4008146015953

- ceramic cooking surfaces (Ø 22 cm) with auto-pan detection
- fast, energy saving and easy to clean
- the heat is generated directly in the base of the saucepan
- minimal loss of energy
- no burnt food on the cooking surface
- illuminated display
- touch control panel
- temperature range from 60 - 240 °C, up to 10 power settings
- 180 minute timer with buzzer and auto switch off
- thermal safety cut-out
- pilot light
- approx. dimensions: W = 28 cm, D = 35 cm, H = 4.2 cm