



DK 1031



Double Induction Cooker

Colour / Material: black

Output: approx. 3400 W

- 2 ceramic cooking surfaces (Ø 21 cm) with auto-pan detection
- fast, energy saving and easy to clean
- the heat is generated directly in the base of the saucepan
- minimal loss of energy from heat dissipation
- no burnt food on the cooking surface
- illuminated display
- touch control panel
- temperature range from 60 - 240 °C, up to 10 power settings
- 180 minute timer with buzzer and auto switch off
- thermal safety cut-out
- pilot light
- dimensions: (W) 59 cm x (D) 35,5 cm x (H) 4,8 cm