manhattan-products.com





8-Port Gigabit Ethernet Switch

Desktop Size, Plastic, IEEE 802.3az (Energy Efficient Ethernet)

Part No.: 560702

Easily add Ethernet-ready devices to your home or office network at Gigabit speeds

The Manhattan 8-Port Gigabit Ethernet Switch is perfect for home office or entertainment system use, as well as many small office applications. Small, powerful and reliable, this Gigabit Ethernet Switch is easy to install and connects up to eight Ethernet-ready devices — computers, gaming systems, network printers, media streamers, network attached storage, Smart TVs ... you name it — at speeds of up to 1000 Mbps (1 Gigabit) over standard Cat5e or Cat6 Ethernet cables.

The auto features of this switch make installation plug and play and hassle free. Plus, it has Green Ethernet technology, allowing it to monitor power usage and turn off unused ports to save electricity.

Features:

- 8-port Gigabit Ethernet switch expands your network in an instant
- Easy plug-and-play installation simply power it up and start using it
- Eight 10/100/1000 auto-sensing ports automatically detect optimal network speeds
- High performance, half and full duplex, with zero packet loss
- Green Ethernet power-saving technology deactivates unused ports
- Supports any combination of 10 Mbps, 100 Mbps or 1 Gbps network devices
- Ultra-compact, fanless design ideal for home and office applications
- Store and forward switching architecture
- Compatible with all Windows and Macintosh systems
- Three-Year Warranty

Specifications:

Standards

- IEEE 802.3 (10Base-T Ethernet)
- IEEE 802.3u (100Base-TX Fast Ethernet)
- IEEE 802.3ab (Gigabit Ethernet)
- IEEE 802.3x (Flow Control and Backpressure)
- IEEE 802.3az (Energy Efficient Ethernet)

General



manhattan-products.com

Connectors: 8 10/100/1000 Mbps RJ45 ports

• Cable: Cat3, 4, 5 UTP/STP

• Duplex modes: all ports (up to 200 Mbps)

• Uplink: all ports Auto MDI/MDX (Auto Uplink)

Switch architecture: store and forward switch technology

• Filter/forward rate:

- 10BaseT: 14,880 pps (packets per second)

- 100Base-TX: 148,800 pps (packets per second)

- 1000Base-T: 1,488,000 pps (packets per second)

• MAC address table: 2,048 entries

Buffer memory: 256 kBytesJumbo frame support: 9 kB

Backplane speed / switch fabric: 16 Gbps

• Certifications: FCC Class B, CE, RoHS

LEDs

Power

Link/Activity

Power

• External AC adapter: 5 V, 1 A

Environmental

• Dimensions: 140 (w) x 78 (l) x 28 (h) mm (5.5 x 3.07 x 1.1 in.)

• Weight: 0.33 kg (0.73 lbs.)

• Operating temperature: 0 – 40?C (32 – 104?F)

• Humidity: 10 – 90% (non-condensing)

Package Contents

• 8-Port Gigabit Ethernet Switch

Power adapter

• User manual







manhattan-products.com







