



Cat6 Shielded Patch Panel

24-Port, FTP, 1U, 90° Top-Entry Punch-Down Blocks

Part No.: **720014**

Lifetime Warranty

Strict manufacturing standards ensure the highest quality in all INTELLINET NETWORK SOLUTIONS products. All items carry a full Lifetime Warranty — the strongest quality commitment anyone can make.

Features:

- Solid and reliable terminations for copper cabling featuring a minimum of 3 mm 50 micro-inch gold-plated jack contacts
- Top-entry punch-down blocks simplify installation
- Compatible with Krone punch-down tools
- Supports 24 to 26 AWG stranded and solid wire
- For use with fully shielded twisted pair (FTP) Cat6 network cable
- Ideal for Ethernet, Fast Ethernet and Gigabit Ethernet network applications
- Meets 19" rackmount standards
- Lifetime Warranty

Specifications:

Standards

- IEEE 802.3 (10Base-T Ethernet)
- IEEE 802.3u (100Base-TX Fast Ethernet)
- IEEE 802.3ab (1000Base-T Gigabit Ethernet)

Certifications

- UL listed
- RoHS compliant
- CE

Environmental

- Dimensions: 482 mm (W) x 43 mm (H) x 109 mm (D) (19 x 1.7 x 4.3 in.)
- Horizontal distance between left and right mounting holes: 465 mm (18.3 in.)
- Vertical distance between top and bottom mounting holes: 32 mm (1.25 in.)
- Weight: 2.16 kg (4.76 lbs.)
- Operating temperature: -40 – 70°C (-40 – 158°F)

Package Contents

- Cat6 Shielded Patch Panel

For more information on Intellinet products, consult your local dealer or visit www.intellinet-network.com.

All names of products or services mentioned herein are trademarks or registered trademarks of their respective owners. Distribution and reproduction of this document, and use and disclosure of the contents herein, are prohibited unless specifically authorized.

- 4 mounting screws
- Grounding wire
- Quick start guide

