

Net Toner and Probe Kit

Tone Generator

Part No.: **515566**

Features:

- Tests datacom, telecom, security, video, and audio networks
- Two position switch for single or multi-tone signal
- LEDs for line polarity, continuity and voltage
- Enhanced talk battery mode provides power for voice communications over inactive pairs
- Testing leads and modular cables for individual wire tests or modular jack tests
- Replaceable plastic tip to prevent accidental shorts
- Trace or identify wire or cables in a bundle or group
- Alligator clips, RJ45 jack, RJ12 plug, optional F-connector
- Lifetime warranty

Specifications:

Net Toner

- Toner Frequency: High alternating 500-781 Hz ; Low alternating 446-657 Hz
- Talk Battery: 9V into a 600 ohms circuit
- Voltage protection: 50 VDC or 24 VAC
- Battery: 9V DC standard or alkaline
- CE Approved: EN 55022 Class B for ITE and EN 55024
- Size: 125 (L) x 68 (W) x 26 (H) mm (4.9 x 2.7 x 1.2 in.)
- Weight: 120g (.37 lb)

Net Probe

- Gain: 30 db
- Tip resistance: 30 ohms (Plastic tip)
- Battery: 9V DC standard or alkaline
- CE Approved: EN 55022 Class B for ITE and EN 55024
- Size: 210 (L) x 40 (W) x 28 (H) mm (8.1 x 1.6 x 1 in.)
- Weight: 140g (.30 lb)

Environmental:

- Operating temperature: 0 – 40°C (32 – 104°F)

Package Contents

- Net Probe
- Net Toner w/ Alligator clips and RJ-12 connector
- Female F-connector to RJ-45 adapter
- Carrying pouch
- User Manual



