



2-Port Mini KVM Switch

2-Port USB, Audio Support

Part No.: **151245**

The Manhattan KVM Switch is a 2-port Mini KVM switch with integrated connection cables. Its USB support on the console side allows you to use a USB keyboard and mouse. It allows you to access, control, boot and reboot two USB-enabled computers with only one USB keyboard, mouse and monitor.

Convenient PC Selection

Quickly and easily switch between workstations using the hotkey.

Audio Switching Offers an Uninterrupted Multimedia Experience

The audio switching function of this KVM Switch allows you to leverage the multimedia systems on each of your two computers. You can monitor the audio output of each computer without disconnecting and reconnecting the audio cables.

Zero Cabling Hassles for KVM Users

This KVM Switch saves you cabling troubles with its two pair of 1.2m (4-ft.) KVM connection cables. In fact, you have zero cabling troubles since you don't have to worry about finding suitable cables to fit — they come attached to the KVM switch!

Features:

- Operate two USB computers with one keyboard, mouse and monitor
- Simply plug in the attached cables — nothing else required!
- Full keyboard and mouse emulation for error-free booting
- Hotkey commands and LED indicators for computer selection
- Audio output for speaker connection
- No software or power required
- Compatible with all operating systems
- Supports resolutions up to 1920 x 1440 pixels
- Lifetime Warranty

Specifications:

General

- PC connections: 2
- Console connections: 1
- PC port connectors:
 - 2 x USB type-A male (keyboard, mouse)

- 2 x HD15 M (video)
- 2 x 3.5 mm jack (sound card input)
- Integrated connection cables: 1.2 m (4 ft.)
- Console port connectors:
 - Keyboard: USB type-A female
 - Mouse: USB type-A female
 - Monitor: HD15 female
 - 1 x 3.5 mm jack (speaker output)
- Computer selection:
 - Via hotkey
- Video resolution: max. 1920 x 1440
- Video bandwidth: max. 250 MHz
- FCC Class B, CE, RoHS

LEDs

- 1 LED per channel

Environmental

- Plastic housing
- Scan interval: 3 seconds
- Dimensions: 85 (W) x 75 (D) x 26 (H) mm (3.4 x 3.0 x 1.0 in.)
- Operating temperature: 0 - 50°C (32 - 122°F)
- Storage temperature: -20 - 60°C (-4 - 140°F)
- Weight: 360 g (12.7 oz.)

Package Contents

- 2-Port Mini KVM Switch
- Quick installation guide



