



IT-250TW

Order No.: 16.3190

PRODUCTINFOS

The music horns from MONACOR are the state-of-the-art solution in order to use the full range of a horn speaker with a clearly extended frequency range.

The 2-way technology with a dynamic cone bass-midrange speaker and a horn tweeter allows for an increase in the sound quality and permits to radiate the keynotes of voices and instruments which cannot be achieved by conventional horn speakers. The music horns are a perfect solution whenever an optimum voice volume and/or a more complete music transmission is required.

Weatherproof horn speaker (music horn), 2-way technology

- 100 V line technique or 8 Ω operation
- IP66 certified
- High-performance music horn at an attractive price
- 16 cm bass-midrange speaker and 25 mm (1") horn
- ABS plastic housing
- Supplied with mounting bracket

TECHNICAL SPECIFICATIONS

IT-250TW

Impedance	8Ω
Operating voltage	100V
Power rating	50/25/12.5/9/4.5/3.5 W (100 V) 50 W (8 Ω)
Peak music power output	-
Frequency range	150-15000Hz
Sensitivity	97dB/W/m
Radiation angle, horizontal	100°
Radiation angle, vertical	60°
Material (housing/cabinet)	ABS
Protective class	IP66
Weather resistance	yes
Mounting facility	mounting bracket
Features	2-way
Replacement voice coil	-
Admiss. ambient temp.	-20 °C to +50 °C
Dimensions	370 x 270 x 305 mm
Weight	4,1kg