

Easy Security Camera Set TX-28

Digital wireless outdoor camera system with recording function











- 7 inch TFT LCD display inclusive one outdoor camera
- Interference-free, waterproof against water jet - dust - touching (IP65)
- Shows up to 4 cameras on the LCD display
- Built-in video recorder and 4 selectable channels
- Recording modes: manual, time programming (timer function) or by motion detection
- Digital transmission range up to 200m in open range
- Infrared night vision
- High sensitivity microphone
- Mobile displayable on iPhone and Android
- Supports MicroSD cards up to 3268
- Easy Plug & Play installation without cable

Article-No. 4433

Technical specifications:

- Camera channels: 2400 2483.5 MHz
- Camera sensor: 1/4" OV7725 CMOS
- Camera resolution: 420 TVL
- Camera min. illumination: 0 LUX (IR on)
- Camera Ø lens / effective pixel: Ø 6mm / 640 (H) x 480 (V)
- Camera S/N ratio: more than 48 dB
- · Camera video output: 1 Vp-p / 75 Ohm
- Camera power supply: DC 5V / 1A
- Monitor display: 7"TFT LCD
- Monitor video format: NTSC / PAL
- Monitor compression format: MPEG-4
- Monitor Video & Audio input / output: 4CH wireless single/1 composite output
- Monitor frame rate: 640 x 480 VGA 20fps / 320 x 240 QVGA 25fps
- Monitor memory card: MicroSD up to 32GB
- Monitor transmission range: ≥ 200m (open range)
- Monitor power supply: DC 12V / 1A

P Package contents:

- 1x Wireless camera
- 1x Wireless Video 7"TFT LCD Receiver
- USB to Mini USB cable (PC connection)
- Cinch cable
- Power adapter for the camera
- Power adapter for the receiver
- 3x screws and 3x dowels
- User Manual

M Meas and Weight:

• Camera

Weight: 270 g

Dimensions: (L) 9,5 x (W) 6,8 x (H) 5,7 cm

Monitor

Weight: 395 g

Dimensions: (L) 20,0 x (W) 12,0 x (H) 2,0 cm

E EAN:

4260101737953

A Additional Camera:

Single "Easy Security Camera TX-28"

EAN Code: 4260101737977 Article No. 4453