



HSM SECURIO C16 - 3.9 mm




HSM SECURIO C16 document shredder

Small, sleek and secure. A great shredder for private use or in a small office. With cutting rollers made from hardened steel and a pressure-sensitive safety element.

Technical data

Order number:	1900111	Intake width:	225 mm
EAN	4026631035583	Container volume / collecting:	25 l
Cutting type:	strip cut	Collection volume in sheets (80 g):	225
Cutting size:	3,9 mm	Noise level (idle operation):	ca. 55 - 60 dB(A)
Security level (DIN 66399):	E-2 P-2 T-2	Weight x Depth x Height:	366 x 258 x 455 mm
Cutting capacity in sheets 80g/m²:	12 - 14	Weight:	4 kg
Power consumption:	185 W	Shredder material:	Paper, Staples and paper clips, Credit card
Voltage / Frequency:	220-240 V / 50 Hz/60 Hz		

Product information



The hardened steel cutting rollers with a lifetime warranty can easily cope with staples and paper clips and guarantee durability.



In stand-by mode, the document shredder does not consume any power.



To empty the waste container, the housing top can be easily removed – a practical, recessed grip facilitates handling.



Quiet operation

The quiet operating mode minimises noise development in the workplace which is an important consideration for your staff.



Blue Angel

The document shredder has been awarded the Blue Angel certificate for its durable construction, low energy consumption and the use of environmentally friendly materials.



Anti-paper jam function

The paper feed with overload protection reduces paper jams and sustains the high throughput of paper.




High level of user safety

User safety is paramount. A slight pressure on the safety element immediately stops the paper feed and prevents unintentional entry into the machine.



Automatic start/stop

The operation is very easy: the device starts automatically when fed paper and automatically stops after shredding is complete.



* HSM SECURIO C14, C16