

## FPMA-D025SILVER

## NEWSTAR FLAT SCREEN DESK MOUNT

Newstar Tilt/Turn/Rotate Desk Mount  
(grommet) for 10-30" Monitor Screen,  
Height Adjustable - Silver



The NewStar desk mount, model FPMA-D025SILVER is a tilt and rotatable desk mount for flat screens up to 30" (76 cm). This mount is a great choice for space saving placement on desks using a grommet mount.

NewStar's versatile tilt (180°) and rotate (360°) technology allows the mount to change to any viewing angle to fully benefit from the capabilities of the flat screen. The mount is easily height adjustable from 37 to 47 centimetres. An innovative cable management conceals and routes cables from mount to flat screen. Hide your cables to keep the workplace nice and tidy.

NewStar FPMA-D025SILVER has one pivot point and is suitable for screens up to 30" (76 cm). The weight capacity of this product is 12 kg each screen. The desk mount is suitable for screens that meet VESA hole pattern 75x75 or 100x100mm. Different hole patterns can be covered using NewStar VESA adapter plates.

By using an ergonomic flat screen mount you prevent neck- and back complaints. Ideal for use in offices and on counters or in a reception area.

### SPECIFICATIONS

Screens	1
Screen size	10 - 30"
Max. weight	12
Desk mount	Desk grommet
VESA minimum	75x75 mm
VESA maximum	100x100 mm
Depth	5 cm
Height	37 - 47 cm
Tilt	180°
Rotation	360°
Color	Silver
Warranty	5 year
EAN code	8717371442361



