

LED Lamps and LED Lampholders - Sealed to IP67

LED Lampholders can be supplied with or without LEDs












































Colours: Red, Yellow Green and Blue LEDs.
(High Intensity is standard. Option of extra super bright).

- ▶ IP67 front bezel sealing
- ▶ LED lampholders
- ▶ Supplied with or without LEDs
- ▶ Black or Chrome finish

Voltages: LEDs are available for direct connection to 2.0/2.2V or 12Vdc.
For other voltages contact sales.

To create a catalogue number:

Refer to the 2 columns below (terminal and type), then state: LED colour and voltage and body finish (Black or Chrome).

▶ TERM	▶ TYPE	▶ PANEL & °C	ILLUM'N OPTIONS	APPROVAL	DIMENSIONS (mm)	
W  LED fitted	(W) 1048 OA 	 8.0  5.5max  T85	 DC  AC	 		
A LED not fitted						
L  LED & Wires fitted	L 1048 OA 	 8.0  5.5max  T85	 DC  AC	 		
W  LED fitted						
A LED not fitted	(W) 1050 OA 	 8.0  7.0max  T85	 DC  AC	 		
A LED not fitted	L 1050 OA 	 8.0  7.0max  T85	 DC  AC	 		

Properties

Sealing

O-ring sealing equivalent to IP67, of both the LED to bezel, and bezel to panel is available where shown.

Polarity

The nylon base mouldings are polarity marked.

Body Material and Finish

Chromed brass or Black oxide coated brass.

Lampholders only

Items prefixed 'A' are supplied without LEDs.

LED wires or PVC covered wire leads

125mm min length wires, 6.3mm standard strip.
Alternative colours, length and strip available.