

Cat6 Wall-mount Patch Panel

12 Port, UTP

Part No.: **560269**

Features:

- Solid and reliable terminations for copper cabling featuring a minimum of 3 mm 50 micro-inch gold plated jack contacts
- Compatible with both 110 and Krone punch down tools
- Supports 22 to 26 AWG stranded and solid wire
- For use with unshielded twisted pair (UTP) Cat6 network cable
- Cat6 performance is in compliance with the ANSI/TIA/EIA 568 B.2-1 standard
- Ideal for Ethernet, Fast Ethernet, and Gigabit Ethernet network applications
- Connects RJ-45 ports to a network
- Lifetime Warranty

Specifications:

Specifications

Standards

- IEEE 802.3 (10Base-T Ethernet)
- IEEE 802.3u (100Base-TX Fast Ethernet)
- IEEE 802.3ab (1000Base-T Gigabit Ethernet)

Certifications

- UL listed
- RoHS Compliant

Environmental

- Dimensions: 254 mm (W) x 82 mm (H) x 47 mm (D)
(10 x 3.2 x 1.9 in.)
- Weight: .337 kg (11.9 oz.)
- Operating temperature: -40°C to 80°C (-40°F to 176°F)

Package contents

- Cat6 Mini Patch Panel
- 2 mounting screws
- Quick Installation Guide

