



Mounting rail, DIN, WxHxD=35x7.5x375mm

Part no. **CL4**
 Catalog No. **038556**
 EL-Nummer (Norway) **0004132217**

Delivery program

Product range			Ci insulated enclosures
Basic function			Basic enclosures
Product function			Mounting system
Accessories			Mounting rail to IEC/EN 60715
Single unit/Complete unit			Modular system
Material			Galvanized steel, 3 mm thick
Information about equipment supplied			Including 2 captive fixing screws
Base height			7.5 mm
Useful length			332 mm
For use with enclosure dimensions			375 mm

Technical data ETIM 7.0

Cabinet enclosures (EG000011) / Component for installation (switchgear cabinet) (EC002620)

Electric engineering, automation, process control engineering / Electrical cabinet, housing, rack / Elements for switching cabinet, housing, rack / Component for installation (electrical cabinet) (ecl@ss10.0.1-27-18-28-11 [ACN627011])

Model			Profile rail
Suitable for enclosure building width		mm	0
Suitable for enclosure building height		mm	0
Suitable for enclosure building depth		mm	0
Width		mm	35
Height		mm	7.5
Depth		mm	375
Max. load capacity		kg	0
Material			Metal
Colour			Other
RAL-number			0

Dimensions

