



VOLTCRAFT®

VOLTCRAFT® - TOP PERFORMANCE IN EVERY WAY

“Since 1982, our product range has been dynamically adapting to the constant changes in the industry. We commit to offering first-class quality to our customers while delivering an excellent cost-performance ratio. This philosophy remains the cornerstone of Voltcraft’s success.”

PB-14 POWERBANK



VERSION 12/21

Nº 1313696

High-quality and high-performance rechargeable spare battery for use on the go. The rechargeable battery fits comfortably into the pocket of your jacket or your handbag, for example, due to its compact size and lightweight design. That way you always have additional energy resources available to power your devices such as a mobile phone, GPS navigator, radio set, etc., sufficiently on the go.

FEATURES:

Compact and lightweight // 2600 mAh capacity // LED capacity indicator //

EQUIPMENT:

Short circuit protection // deep discharge and overload protection // LED capacity indicator // high-quality built-in rechargeable Samsung battery //

PACKAGE CONTENTS:

Powerbank PB-14 // micro-USB on USB cable // operating instructions //

TECHNICAL DATA:

Capacity:	2600 mAh
Number of charging channels:	1
Outputs:	USB connector type A
Battery type:	Li-Ion
Operating voltage:	5V via USB
Loading current (max.):	1000 mA
Colour:	White
Range of operating temperature:	-20 to +60 °C
Dimensions (L x W x H):	94 x 25 x 25 mm
Weight:	70 g



Legal notice

This data sheet is published by Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92240 Hirschau (www.conrad.com). All rights including translation reserved. Reproduction by any method, e.g. photocopy, microfilming, or the capture in electronic data processing systems require the prior written approval by the editor. Reprinting, also in part, is prohibited. This data sheet represent the technical status at the time of printing.

© Copyright 2022 by Conrad Electronic SE

1313696_V2_1221_01_PIX_ds