



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NUMBER	MAXIMUM CABLE DIAMETER	PANEL DIMENSIONS		WEIGHT LBS./100 PCS. (g)
		THICKNESS	HOLE SIZE	
HWS2819	0.19 (4.8)	0.03/0.08 (0.8/2.0)	0.187/0.192 (4.7/4.9)	0.08 (35)



NOTE:

- SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE AND PART COLOR.

(DIMENSIONS IN PARENTHESES ARE METRIC)

CAD FILENAME/LAYERS  
G00239BV\_PB\_HWS2819\_02

**PANDUIT** CORP. TINLEY PARK, ILLINOIS

HORIZONTAL WIRE SADDLE  
HWS2819

UNLESS OTHERWISE SPECIFIED,  
DIMENSIONAL TOLERANCES ARE:  
(.X) ± N/A (.XXX) ± .010 (.25)  
(.XX) ± .02 (.5) ANGLES ± N/A

UNLESS OTHERWISE SPECIFIED,  
ALL DIMENSIONS ARE GIVEN  
IN INCHES, THIRD ANGLE PROJECTION.

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP
2	6/26/01	LGG		REVISED DRAWING FOR WEB	GB0239BV	2		
1	4/10/95	DWP		ADDED 4 DIMENSIONS	GB0239BV	1		
R	5/5/94	KLJ		INITIAL RELEASE	GB0239BV	R		

DRAWN BY  
KLJ  
DATE  
5/5/94  
CHK'D

MAT'L:  
NYLON 6/6

SCALE  
2/1  
DRAWING NO.  
GB0239BV  
DWG  
A  
SIZE