



2

1

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT * PART NO.	MAX. COMBINED BUNDLE DIA. D1 + D2 in (mm)	A in. (mm)	B in. (mm)	C in. (mm)	D in. (mm)	E in. (mm)	F in. (mm)	MIN. LOOP TENSILE lbs (N)	CROSS- SECTION	WEIGHT lbs/100pcs (g)
PLB2S	1.8 (45.7)	.052 (1.3)	.190 (4.8)	.465 (11.8)	.220 (5.6)	.320 (8.1)	7.6 (193)	50 (222)	STANDARD	.34 (154)
PLB3S	3.0 (76.2)	.052 (1.3)	.190 (4.8)	.465 (11.8)	.220 (5.6)	.337 (8.6)	11.8 (300)	50 (222)	STANDARD	.47 (214)
PLB4S	4.1 (104.1)	.052 (1.3)	.190 (4.8)	.465 (11.8)	.220 (5.6)	.337 (8.6)	14.8 (376)	50 (222)	STANDARD	.58 (262)

\* SEE [www.panduit.com](http://www.panduit.com) FOR CURRENT PART NUMBER SUFFIX DESIGNATION AND FOR PACKAGE SIZE AND PART COLOR

D10100DA/16

						TITLE <b>BOW-TY CABLE TIES PLB SERIES</b> CUSTOMER DRAWING						
						ITEM REVISION NAME 10B0150W/00						
						DATASET FILE NAME 10B0150W_DC_PLB/00A						
						UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [ mm ] .x ± .xx ± .02 [ .5 ]      .xxx ± .020 [ .51 ] ANGLES ±				MATERIAL: NONE		
6    11.20.14    BDK    MPH    JADE    UPDATED TITLE BORDER AND UPDATED NOTES    SS-21645						THIRD ANGLE PROJECTION				DRAWING NUMBER: <b>SS-21645</b>		
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY	DATE	CHK	SCALE	SHT 1 OF 1	SIZE
							KEM	4/6/87	HVP	NONE		A

2

1