

# KERN OBB-A1218

**KERN**

Individual plug-in phase-contrast unit with  $\infty$  PH plan objective 40 $\times$ , for 40 $\times$



## Category

|                  |                     |
|------------------|---------------------|
| Brand            | Optics              |
| Product category | Optical Instrument  |
| Product group    | Phase contrast unit |

## Environmental conditions

|                           |       |
|---------------------------|-------|
| Storage temperature [Min] | -5 °C |
| Storage temperature [Max] | 40 °C |

## Packing & Shipping

|                              |                |
|------------------------------|----------------|
| Delivery time                | 1 d            |
| Dimensions packaging (W×D×H) | 170×120×70 mm  |
| Shipping method              | Parcel service |
| Net weight approx.           | 0,30 kg        |
| Gross weight approx.         | 1,00 kg        |
| Shipping weight              | 1 kg           |

## Product information

|                      |                          |
|----------------------|--------------------------|
| GTIN/EAN number      | 4045761167506            |
| REACH classification | no prohibited substances |

## Pictograms

### STANDARD

