KERN **OBL 127**

The flexible laboratory assistant with infinity optical system and fixed, pre-centred Koehler illumination



Category

Brand	Optics
Product categoriy	Microscope
Product group	Compound microscope
Product family	OBL-12

Construction

Dimension (W×D×H)	395×200×380 mm
Optical system	Infinity
Tube type	Binocular
Tube angle of inclination	30°
Tube 360° rotation	✓
Tube type	Butterfly
Contrasting methods	Bright field Darkfield (optional) Polarisation (optional) Fluorescent (optinal) Phase contrast (optional)
Standard objectives	4× 10× 40× 100×
Lens quality	Infinity E-Plan
Nosepiece screw-in locations	4
Interpupillary distance [Min]	50 mm
Interpupillary distance [Max]	75 mm
Diopter adjustment	one-sided
Diopter adjustment [Min]	-5
Diopter adjustment [Max]	5
Colour temperature	6000 K

Ocular

Ocular type	Eyepiece HWF 10x / Ø 20mm with anti-fungus, high eye point
Ocular field width	HWF
Eye point	High Eye Point
Ocular magnifications	10x
Ocular visual field	20 mm
Ocular diameter	23,2 mm

Objective

Objectives - Details	Objective Infinity E-Plan 10x / 0,25 anti-fungus Objective Infinity E-Plan 100x / 1,25 oil, spring, anti-fungus Objective Infinity E-Plan 4 x / 0,11 anti-fungus Objective Infinity E-Plan 40x / 0,65 spring, anti-fungus
Objectives magnifications	4x / 10x / 40x / 100x

Illumination

Illuminance	Transmitted light
Illumination type transmitted light	LED
Illumination intensity transmitted light	3 W
Illumination dimmable	Transmitted light
Koehler illumination	✓
Filter possible	✓
Aperture diaphragm	✓
Field diaphragm	✓

Focussing

Field of view [Min]	0,2 mm
Field of view [Max]	5 mm
Torque regulation	✓
Fine drive minimum	0,002 mm
Focusing mechanism	coaxial coarse and fine drive

Condensor

Condensor type	Abbe

Power Supply

Supplied power supply	Power supply unit
Power supply type	Power adapter

KERN **OBL 127**

The flexible laboratory assistant with infinity optical system and fixed, pre-centred Koehler illumination

Plug-in power supply / adapter for countries - included with the delivery	EURO
Plug-in power supply / adapter for countries - optional	AUS UK US CH
Power supply – Cable length	150 cm
Input voltage power supply / power [Max]	100 V - 240 V AC 50/60 Hz 0,3 A
Power supply cable removable	removable
Input voltage device / power [Max]	5 V, 1 A

Environmental conditions

Storage temperature [Min]	-5 °C
Storage temperature [Max]	40 °C

Approval

CE mark	✓

Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	435×400×280 mm
Shipping method	Parcel service
Net weight approx.	7 kg
Gross weight approx.	8 kg
Shipping weight	9,7 kg

Product information

GTIN/EAN number	4045761267756
REACH classification	no prohibited substances

Pictograms

STANDARD



OPTION

