


SPECIFICATION FOR APPROVAL

TO: 頂興


2/1

PART NAME	EMI FILTER		FTB-5551
	YF01T6	SAMPLE DATE	NOV-07-2013
MODEL NO		OUR DRAWING NO	YDR-00023d

1. PHYSICAL DIMENSIONS:(mm)



2. SCHEMATIC:



REPORTED BY	CHECKED BY	APPROVED BY	3
			2
			REV. 1

SPECIFICATION FOR APPROVAL

TO: 頂興

2/2

PART NAME	EMI FILTER		FTB-5551
	YF01T6	SAMPLE DATE	NOV-07-2013
MODEL NO		OUR DRAWING NO	YDR-00023d

3.ELECTRICAL CHARACTERISTICS:

- 3-1.RATED VOLTAGE 125/250VAC
- 3-2.RATED CURRENT 1A
- 3-3.OPERATING FREQUENCY 50/60Hz
- 3-4.LEAKAGE CURRENT: EACH LINE TO GROUND
250VAC 50Hz 0.8mA MAX
- 3-5.HIPOT RATING:(FOR ONE MINUTE)
LINE TO LINE 1450VDC
LINE TO GROUND 1800VAC
- 3-6.INSULATION RESISTANCE 250VDC/100MOHM MIN
- 3-7.DIRECT CURRENT RESISTANCE 0.5 OHM MAX
- 3-8.OPERATING TEMPERATURE -25 TO +85°C

4.SAFETY COMPLIANCE:

UL FILE NO:E134751
CSA FILE NO:LR95210
VDE FILE NO:40007880
CE

5. INSERTION LOSS IN dB:

FREQUENCY	0.15MHZ	0.5MHZ	1MHZ	5MHZ	10MHZ	30MHZ	50MHZ
common mode	45	48	51	47	48	41	26
normal mode	8	20	33	36	34	30	27

■ ABOVE TABLES ARE REFERENCE ONLY.

REPORTED BY	CHECKED BY	APPROVED BY	3
			2
			REV. 1