







- NOTES:
 1. DIMENSION SHALL BE INTERPRETED PER ASME Y14.5-2009.
 2. PITCH: 5.0MM, POLES: 2-22P
 3. RATED VOLTAGE/CURRENT: UL 300V/10A VDE 250V/17.5A
 4. OPERATION TEMPERATURES: -30°C~+120°C
 5. WITHSTANDING VOLTAGE: AC2000V/1MIN.
 6. INSULATION RESISTANCE: 5000MΩ/DC1000V
 7. WIRE RANGE: 22~14AWG, 1.5MM²
 8. TORQUE VALUE: M2.5, 4.08kgf.cm
 9. UNDIMENSIONED TOLERANCES:

PITCH RANGE IN MM	NOMINAL DIMENSION RANGE IN MM				—
	OVER TO	OVER TO	OVER TO	OVER TO	
6 TO 10	10 TO 24	30 TO 60	60 TO 100	100 TO 150	—
±0.10	±0.15	±0.25	±0.30	±0.50	±1.00, 10/10



REVISION RECORD				
REV	ECN	DESCRIPTION	DRFT	DATE
△		Drawing Revise	Haoyh	03/20/06*
△		工程变更	CSX	07/13/06*
△		增加VDE、CE标志	LJH	12/03/07*
△	11-0160	去掉工艺槽	ZXX	07/03/11*
△	14-0322	产品变形度由0.05/10变为0.10/10	WYJ	09/19/14*

ITEM	NAME OF PART	NO. OF PART	Q'TY	MATERIAL	NOTES
1	DG301R-5.0-Housing	4005A0YXXA(H)	1	PBT	UL94V-0
DETACHED LISTS TOLERANCES EXCEPT AS NOTED ANGLES ± 1° THIRD ANGLE PROJECTION DO NOT SCALE DRAWING					
MATERIAL:		PART NO.:		NAME:	
Steel		Cr-3+Zn		DEGSON 宁波高正电子有限公司	
Stainless steel				DEGSON DEGSON ELECTRONICS CO., LTD	
Brass		Sn plated		DG301R-5.0-XXP-1Y-00A(H)	
Sn plated				TITLE: ASSEMBLY DRAWING	
4 DG301-Screws		S000001420(H)		DRAWING NO.: DG301R-E02	
3 DG301-Spring		X000000250(H)		SCALE N/A	
2 DG301R-Pin		4005B00020(H)		REV T5	
8		7		SHEET 1/1	