



Leiterquerschnitt / wire gauge: 1,5mm<sup>2</sup> / AWG 16  
 Abisolierlänge / stripping length: 9mm

All Dimensions in mm Original Size DIN A 4			Techn. Character.			Nicht tolerierte Masse / Free size tolerances				
				Dat.	Name	Massstab / Scale  <b>5:1</b>	Han C Buchsenkontakt, gedreht 40A Han C female contact, turned 40A versilbert / silver plated			
			Detail.	20.12.05	Ho					
			Insp.		SP					
			Stand.							
413759	19.03.08	Rull	HARTING Electric GmbH & Co. KG D-32339 Espelkamp				<b>TB 09 32 000 6204</b>			Blatt / page /
411928							Sub. TB 09 32 000 620. v. 18.06.99			
Mod.	Dat.	Name								