



GCB-50B

Order No.: 11.8960

PRODUCTINFOS

Swivel Castors from Blicke,

for transporting e.g. PA speaker systems or cases.

- Castor wheels with plain bearing and ball bearing guidance
- All-rubber castor wheels
- Zinc-plated metal parts

TECHNICAL SPECIFICATIONS

GCB-50B

Type	swivel castor with brake
Wheel diameter	50 mm
Height	71 mm

GCB-50B

Support area	60 x 60 mm
Max. load	40 kg
Castor wheel material	all-rubber, grey, non-marking
Pos.	B

* **Important Notice:** The retail prices shown here are non-binding recommendations that retailers can charge their customers. They are not part of any specific offer or advertisement. These prices include all charges as well as VAT, but do not cover any additional delivery and shipping costs. Our latest price lists for the retail market include all applicable delivery and payment terms for retailers.