



19" Network Cabinet

26U, IP20-rated housing, Flatpack, Gray

Part No.: **712965**

EAN-13: 0766623712965 | UPC: 766623712965

The Intellinet Network Solutions network cabinets offer you a flexible and comprehensive solution for your network installations. Our service starts with the shipping condition – get the completely assembled cabinet delivered or save space and money with the flatpack version.

In terms of housing, you have numerous 19" options with installation depths that range from 600 to 800 mm: With heights from 16 to 42 units in black (RAL9005) or gray (RAL7035), we offer you a solution for every need. The removable side panels and the lockable tempered-glass door make cabling and component exchange particularly easy.

In material and workmanship, we provide top quality. Part of that is a cold-rolled steel frame, zinc-plated 19" mounting rails and antistatic powder coating on all panels.

Features:

- Ideal for all 19 in. rackmount applications
- Maximum static load of 1500 kg
- Tempered-glass door
- Zinc-plated 19 in. mounting rails
- Antistatic powder coating on all panels
- Panels with up to 2 mm steel thickness
- Reversible front door
- IP20-rated housing
- Easily removable side and rear panels
- Multi-point door lock
- Two apertures allow cable inlet from top or bottom
- Ventilation slots provide excellent airflow
- Ships flatpacked
- Three-Year Warranty

Specifications:

General

- 19 in.
- Height: 26U
- Color: Gray RAL7035
- Certifications: RoHS, UL, Gost-R
- Protection rating: IP20

Dimensions

- 800 (L) x 600 (W) x 1322 (H) [mm]
- 31.05 (L) x 23.62 (W) x 52.05 (H) [in]

Package Contents:

- 4 depth-adjustable mounting rails
- 4 adjustable supporting feet
- Installation hardware



