



19" Wallmount Cabinet

12U, Flatpack, Black

Part No.: **711883**

The Intellinet wall mount cabinets offer you a flexible and comprehensive solution for your network installations. Our service starts with the shipping condition – get the completely assembled cabinet delivered or save space and money with the flat-pack version. In terms of housing, you can choose from among the extra-compact 10U cabinets and numerous 19U versions, with installation depths that range from 300 to 600 mm. Heights from 6 to 20 units in black (RAL9005) or (RAL7021) & gray (RAL7035).

We offer you a solution for every need.

Various options include:

Removable side panels (some lockable).

Tempered/Toughened glass doors.

Double Section, making cabling and component exchange simple.

In material and workmanship, we provide top quality. Part of that is a cold-rolled steel frame, zinc-plated 19U mounting rails and antistatic powder coating on all panels.

Features:

- Ideal for 19" rackmount applications
- Maximum static load of 60 kg
- Tempered-glass door can be opened more than 180°
- Cable entry via rear or top panel
- Cold-rolled, galvanized SPCC steel with up to 1.2 mm thickness
- Antistatic powder coating on all panels
- Reversible Front door
- Easily removable side panels
- Ships flatpacked

For more information on Intellinet products, consult your local dealer or visit www.intellinet-network.com.

All names of products or services mentioned herein are trademarks or registered trademarks of their respective owners. Distribution and reproduction of this document, and use and disclosure of the contents herein, are prohibited unless specifically authorized.

- Three-Year Warranty

Specifications:

General

- 19"
- Height: 12U
- Color: Black RAL9005
- Complies with: ANSI/EIA RS-310-D; IEC60297-2; DIN41494, Part 1; DIN41494, Part 7

Dimensions

- 635 (h) x 570 (w) x 600 (d) mm
- 25 (h) x 22.4 (w) x 23.6 (d) in.

Package Contents

- 2 depth-adjustable mounting rails
- Installation hardware



