



19" Wallmount Cabinet

20U, Assembled, Black

Part No.: **712057**

The Intellinet wall mount cabinets offer you a flexible and comprehensive solution for your network installations. Our service starts with the shipping condition – get the completely assembled cabinet delivered or save space and money with the flat-pack version. In terms of housing, you can choose from among the extra-compact 10U cabinets and numerous 19U versions, with installation depths that range from 300 to 600 mm. Heights from 6 to 20 units in black (RAL9005) or (RAL7021) & gray (RAL7035). We offer you a solution for every need.

Various options include:

Removable side panels (some lockable).

Tempered/Toughened glass doors.

Double Section, making cabling and component exchange simple.

In material and workmanship, we provide top quality. Part of that is a cold-rolled steel frame, zinc-plated 19U mounting rails and antistatic powder coating on all panels.

Features:

- Ideal for 19" rackmount applications
- Maximum static load of 60 kg
- Tempered-glass door can be opened more than 180°
- Cable entry via rear or top panel
- Cold-rolled, galvanized SPCC steel with up to 1.2 mm thickness
- Antistatic powder coating on all panels
- Reversible Front door
- Easily removable side panels
- Ships assembled
- Three-Year Warranty

Specifications:

General

- 19"
- Height: 20U
- Color: Black RAL9005
- Complies with: ANSI/EIA RS-310-D; IEC60297-2; DIN41494, Part 1; DIN41494, Part 7

Dimensions

- 990 (h) x 600 (w) x 600 (d) mm
- 39 (h) x 23.6 (w) x 23.6 (d) in.

Package Contents

- Wall mount Cabinet with 4 mounting rails
- Installation hardware including tool, 20x M6 Sets and 6x Keys

