



Configuration module for configuring ramp time, Motor protection, terminal mode of operation for DE1 variable speed starter

Part no. DXE-EXT-SET
Catalog No. 174621
Alternate Catalog No. DXE-EXT-SET
EL-Nummer (Norway) 4110117

Delivery program

Description		With selector switch for ramp time and operating mode With potentiometer for motor protection and fixed frequency
For use with		DE1, DE11
Connection technique		Plug-in module (front)

Design verification as per IEC/EN 61439

Technical data for design verification		
Operating ambient temperature min.	°C	-10
Operating ambient temperature max.	°C	50

Technical data ETIM 7.0

Low-voltage industrial components (EG000017) / Accessories for frequency controller (EC002025)		
Electric engineering, automation, process control engineering / Electrical drive / Static frequency converter / Static frequency converter (accessory) (ecl@ss10.0.1-27-02-31-92 [AFR303003])		
Type of accessory		Other

Approvals

Product Standards		UL 508C; CSA-C22.2 No. 274; IEC/EN61800-3; IEC/EN61800-5; CE marking
UL File No.		E172143
UL Category Control No.		NMMS, NMMS7
CSA File No.		UL report applies to both US and Canada
North America Certification		UL recognized, certified by UL for use in Canada
Specially designed for North America		No
Suitable for		Branch circuits

Dimensions



