



| REVISION |                 |           |           |
|----------|-----------------|-----------|-----------|
| REV      | DESCRIPTION     | DATE      | SIGNATURE |
| A        | Initial release | 2025/12/4 | Join      |



| USB A    | Wire Color | Micro B |
|----------|------------|---------|
| P1       | Red(Vbus)  | P1      |
| P2       | White(D-)  | P2      |
| P3       | Green(D+)  | P3      |
| /        | /          | P4      |
| P4 Shell | GND Shield | P5      |

Wiring Method

|    |          |                       |     |          |               |       |                                  |                  |             |                          |            |
|----|----------|-----------------------|-----|----------|---------------|-------|----------------------------------|------------------|-------------|--------------------------|------------|
| ⑥  | S00-059  | Micro B Outer Molding | 1   | PVC      | Black         | TITLE | 1344037 USB A-Micro B Cable 1.0m |                  |             | DRAWING No. SHEET<br>1/1 |            |
| ⑤  | S00-046A | Micro B Inner Molding | 1   | PE       | ---           |       |                                  |                  |             |                          |            |
| ④  | 311-025  | Micro B Connector     | 1   | Steel    | Nickel Plated |       |                                  |                  |             |                          |            |
| ③  | S00-045  | USB A Outer Molding   | 1   | PVC      | Black         |       |                                  |                  |             |                          |            |
| ②  | S00-055A | USB A Inner Molding   | 1   | PE       | ---           | UNIT  | SCALE                            | TOL UNLESS NOTED | APPROVED BY | CHECKED BY               | DRAWING BY |
| ①  | 311-136  | USB A Connector       | 1   | Steel    | Nickel Plated | mm    | Free                             | ±0.1             |             | Join                     | Join       |
| No | PART No  | COMPONENTS            | QTY | MATERIAL | FINISH        |       |                                  |                  | 2025/12/4   | 2025/12/4                | 2025/12/4  |