



MP9-6A

Nominal Voltage (V) 6V

Nominal Capacity

20hour rate (0.45A to 5.25V)	9Ah
10hour rate (0.9A to 5.25V)	9Ah
5hour rate (1.53A to 5.25V)	7.65Ah
1C (9A to 4.80V)	4.05Ah
3C (27A to 4.80V)	3.24Ah

Weight 1.57kg(3.47Lbs.)

Internal Resistance (at 1KHz) 10 mΩ

Maximum Discharge Current for 30 seconds : 180A

Maximum Discharge Current for 5 seconds : 360A

Operating Temperature Range

Charge	0°C (32°F) to 40°C (104°F)
Discharge	-15°C (5°F) to 50°C (122°F)
Storage	-15°C (5°F) to 40°C (104°F)

Charge Retention (shelf life) at 20°C (68°F)

1 month	92%
3 month	90%
6 month	80%

Charging Methods at 25°C (77°F)

Cycle use:
 Charging Voltage 7.20 to 7.50V
 Maximum Charging Current: 2.7A
Standby use:
 Float Charging Voltage 6.75 to 6.90V

Life expectancy :

Cycle Use:
 100% depth of discharge 200 cycles
 80% depth of discharge 225 cycles
 50% depth of discharge 500 cycles

Standby Use: 3-5 years

Case Material ABS
 (Option: 94-HB & 94V-0 flame retardant case)

Terminal F1

