



Type: 57647
Designation:..... Plug charger

Systems to charge: Ni-MH
Cell sizes:..... AAA, AA
Cell Configurations:..... AAA, AA, 2/4 pcs

Dimensions: **Charger:**

Length:..... 121mm
Width:..... 74mm
Height:..... 68mm
Weight:..... 107g

Charging methods: **AC 100-240V 50/60Hz**

Maintenance Charge:

AA:..... Current: 350 mA ± 10%
AAA:..... Current: 150 mA ± 10 %

Current: 0 mA
Current: 0 mA

Housing:

Housing Material:..... ABS V-0
Casing color:..... black, grey

Indications: LED display

AAA, AA, cell mix:..... LED solid on = Charge
AAA, AA, cell mix:..... LED off= charge off
AAA, AA, cell mix:..... LED flash= short circuit

Protective Functions:

Reverse protection
Short circuit protection

Power:

Primary:..... 100 - 240 VAC 50/60 Hz
Secondary:..... 2.8V

Cut off criteria:

Ni-MH standard cells:... Timer: backup timer 8 hours

No publication or circulation of data to third parties without consent of VARTA Consumer Batteries